


**Flap wheel (A), 60 grit, Head Ø×head width: 40X15 mm****Order data**

Order number	554100 40X15
GTIN	4045197235466
Item class	52E

Description**Version:**

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Grinding medium code: A

Shank Ø: 6 mm

recommended speed: 12000 rpm

maximum speed: 19100 rpm

Technical description

Head width	15 mm
Grit	60
maximum speed	19100 rpm
recommended speed	12000 rpm
Shank Ø	6 mm

Head Ø	40 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	60 grit
Type of product	Flap wheel