




Flap wheel (A), 120 grit, Head Ø×head width: 50X20 mm



Order data

Order number	554300 50X20
GTIN	4045197240774
Item class	52E

Description

Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Grinding medium code: A

Shank Ø: 6 mm

recommended speed: 9000 rpm

maximum speed: 15300 rpm

Technical description

recommended speed	9000 rpm
Grit	120
maximum speed	15300 rpm
Head width	20 mm
Shank Ø	6 mm

Head Ø	50 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	120 grit
Type of product	Flap wheel