


HOLEX**Flap wheel (A), 120 grit, Head Ø×head width: 50X30 mm****Order data**

Order number	554300 50X30
GTIN	4045197525840
Item class	52E

Description**Version:**

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Grinding medium code: A

Shank Ø: 6 mm

recommended speed: 9000 rpm

maximum speed: 15300 rpm

Technical description

Grit	120
Head width	30 mm
maximum speed	15300 rpm
recommended speed	9000 rpm
Shank Ø	6 mm

Head Ø	50 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	120 grit
Type of product	Flap wheel