

Garant**Grinding point coarse, AR, Type: SP1320****Order data**

Order number	550900 SP1320
GTIN	4045197239464
Item class	51E

Description**Version:**

GARANT grinding points (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Ceramic bonded grinding points in **pink aluminium oxide (AR)**. Medium-hard version.

Coarse grit. Shank length 40 mm.

Application:

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

Technical description

Grit designation	coarse
Shaft length	40 mm
Head Ø	13 mm
Shank Ø	6 mm
Head length	20 mm
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A

Product name attribute	AR
Type of product	Grinding point