

**Flap wheel Fleece sinusoidal, medium, Head Ø×head width: 100X50mm****Order data**

Order number	554976 100X50
GTIN	4045197678867
Item class	52E

**Description****Version:**

Sinusoidal abrasive fleece without cut edges. Shank Ø 6 mm.

**Application:**

For matting and **polishing** without abrupt changes in texture.

**Technical description**

Head width	50 mm
recommended speed	3000 min <sup>-1</sup>
maximum speed	6000 min <sup>-1</sup>
Shank Ø	6 mm
Head Ø	100 mm
Grinding medium code	A
Grit equivalent	180
Grit designation	medium
Product name attribute	medium

Type of product

Flap wheel

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		