

**Fleece velour-backed abrasive disc, Ø 125 mm, Grit equivalent: 180****Order data**

| | |
|--------------|---------------|
| Order number | 566950 180 |
| GTIN | 4045197566232 |
| Item class | 52E |

Description**Version:**

Fleece velour-backed abrasive discs with through-stitched backing for hook and loop fastener. With removable centre for more precise positioning and attachment of the disc to the backing pad (**approx. 50 % reduction in vibration level with velour-backed abrasive discs No. 566965**).

Application:

On angle grinders with hook and loop fastener backing pad No. 566960 or 566965. For **finishing, matting, smoothing** with significant reduction in roughness, and for **light cleaning** (such as removal of discolouration) and **deburring tasks**.

Note:

See No. **567705ff** onwards for velour-backed abrasive discs for rough abrasion.

maximum circumferential speed: 40 m/s

Grit designation: medium

Version: A medium

Colour: red

Technical description

| | |
|------------------|--------|
| Grit designation | medium |
|------------------|--------|

| | |
|---|--------------------|
| Version | A medium |
| Grit equivalent | 180 |
| Colour | red |
| Disc Ø | 125 mm |
| Grinding medium code | A |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 125 mm |
| maximum circumferential speed | 40 m/s |
| Type of product | Non-woven abrasive |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable | | |
| Uni | suitable | | |
| wet maximum | suitable only under restricted conditions | | |
| dry | suitable | | |

Accessories

Hook and loop backing pad with Thread M 14 External Ø
125 mm

566960 125

Hook and loop backing pad with Centring and M 14 thread
External Ø 125 mm

566965 125