

**Garant**

**Carbide boring bar E.. SDQCR 107,5°, for indexable inserts DC., right-hand,  
Shank Ø / insert size: 20/11mm**


**Order data**

Order number	260320 20/11
GTIN	4045197877727
Item class	21T

**Technical description**

Clamping height $L_2$	18.9 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Overhang $L_1$	52 mm
Centre offset $L_3$	12.5 mm
Insert size	11 mm
Setting angle $\kappa$	107.5 degrees
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Overall length $L$	250 mm
ISO code toolholder	E20S SDQCR/L11
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15