

**Garant**

**Carbide boring bar E.. SDQCL 107,5°, for indexable inserts DC., left-hand,  
Shank Ø / insert size: 20/11mm**


**Order data**

Order number	260321 20/11
GTIN	4045197877789
Item class	21T

**Technical description**

Overall length L	250 mm
suitable indexable insert	DC.. 11T3..
Overhang L <sub>1</sub>	52 mm
ISO code toolholder	E20S SDQCR/L11
Insert size	11 mm
Clamping height L <sub>2</sub>	18.9 mm
Setting angle κ	107.5 degrees
Pack of insert screws	269028 8
Minimum pre-drill Ø D <sub>min</sub>	25 mm
Centre offset L <sub>3</sub>	12.5 mm
Shank Ø D <sub>s</sub>	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15