

Garant

Clamping toolholder SDNCN 62,5°, for indexable inserts DC., neutral, Shank / insert size: 10/07mm



Order data

Order number	260300 10/07
GTIN	4045197878236
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
Insert size	7 mm
Overhang L ₁ neutral holders	9.5 mm
Shank size	10 mm
Overall length L neutral holders	70 mm
ISO code toolholder	SDNCN 1010E07
Functional width L ₄ neutral holders	5 mm
Pack of insert screws	269028 22
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	62.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15