



Double ratchet ring spanner, Widths across flats: 17X19mm



Order data

| | |
|--------------|---------------|
| Order number | 614843 17X19 |
| GTIN | 4045197879493 |
| Item class | 62A |

Description

Version:

Drop-forged. With close tolerance jaw widths. Reversible for left- and right-hand tightening, plus centre position. With unequal jaw widths, deep cranked. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

| | |
|-------------------------------|-----------------------|
| maximum ring height h_2 | 24 mm |
| maximum ring height h_1 | 23 mm |
| Width across flats 2 | 19 mm |
| Width across flats 1 | 17 mm |
| Width across flats | metric |
| maximum ring \varnothing D1 | 33 mm |
| maximum ring \varnothing D2 | 35 mm |
| overall length L | 290 mm |
| No. of teeth | 72 |
| Working arc | 5 degrees |
| Manufacturing process | drop forged |
| Material | Chrome vanadium steel |
| Surface | matt chrome-plated |

| | |
|--------------------|---------|
| Ring end cranked | yes |
| Ratchet reversible | no |
| Type of product | Spanner |