

Garant**GARANT Master Tap machine tap HSS-E-PM Form C, AlTiX, M: M14****Order data**

Order number	135960 M14
GTIN	4045197900050
Item class	11I

Description**Version:**

Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for a high degree of wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Corresponds to **ISO 2X/6HX**.

Thread type: M

Tool material: HSS E PM

Standard: DIN 376

Tolerance class: ISO 2X 6HX

Thread pitch: 2 mm

Overall length L: 110 mm

Shank Ø D_s: 11 mm

Shank square □: 9 mm

Tapping hole Ø: 12 mm

Technical description

Number of clamping slots	3
Overall length L	110 mm
Number of cutting edges Z	3
Shank Ø D _s	11 mm
Thread pitch	2 mm
Tolerance class	ISO 2X 6HX

Thread depth	35 mm
Tapping hole Ø	12 mm
Standard	DIN 376
Shank square □	9 mm
Tool material	HSS E PM
Thread Ø	14 mm
Thread type	M
Thread size	M14
Coating	AlTiX
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	C
Helix angle	40 °
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	Suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P

Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		