

**Flap wheel roller M14 Fleece/fabric, Ø 100 × 50 mm, Grit equivalent: 80CRS****Order data**

Order number	566372 80CRS
GTIN	4045197924605
Item class	52M

Description**Version:**

Strips arranged in a fan form around the axis of the tool. **M14 direct mounting.**

Combination of **abrasive cloth and fleece.**

Application:

Removes scratches, gives a brushed matt effect.

Technical description

recommended speed	2800 min ⁻¹
Grit equivalent	80
maximum speed	6000 min ⁻¹
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Thread	M14
Roller Ø	100 mm

Roller width	50 mm
Product name attribute	Ø 100 × 50 mm
optimised for material	Steel
optimised for material	INOX
maximum circumferential speed	30 m/s
Type of product	Flap wheel roller fabric, slit

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Carbide (HM)	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
dry	suitable		