

Garant**Pipe cutter universal****Order data**

Order number	818150
GTIN	4045197595645
Item class	81C

Description**Version:**

Extremely sturdy design for very heavy duties. Clean and reliable cut thanks to 4 guide rollers in a row.

Die-cast aluminium body. Quick adjustment spindle with ratchet and spring retraction. With spare cutter wheel No. 818110.

Advantage:

Long working lives due to **TiN coated** cutter wheel. Saves effort and time due to:

- **Ergonomic handle**
- **Lightweight design**
- **Needle bearings on the guide rollers and cutter wheel**
- **Detachable manual deburrer with TiN-coated S20 blade.**

Application:

Multi-functional use for cutting stainless steel, aluminium, brass, and copper pipes.

Technical description

for pipe outer Ø	6 - 76 mm
Cutter wheel width	6.2 mm
Cutter wheel bore	4.85 mm
Cutter wheel Ø	19 mm
Weight	880 g
Length	245 - 325 mm

Height	40 mm
Width	100 mm
Number of guide rollers	4
Number of cutter wheels	1
suitable for pipe material	Brass
suitable for pipe material	Copper
suitable for pipe material	VA
suitable for pipe material	Aluminium
with ratchet function	no
Type of product	Pipe cutters

Accessories

Stainless steel inner / outer deburrer for pipe Ø up to 35 mm	814920 35
Stainless steel inner / outer deburrer for pipe Ø up to 54 mm	814920 54
Spare cutter wheel	818110
Wheel pin	819630
Stainless steel inner / outer deburrer for pipe Ø up to 54E mm	814920 54E
Guide roll set with needle bearings 16 pieces	818035