

Garant**Double ratchet ring spanner, 15° offset, Jaw widths: 17X19mm****Order data**

Order number	614845 17X19
GTIN	4045197416223
Item class	61B

Description**Version:**

Drop forged, with particularly free-running sturdy ratchet ring at each end. Reversible for left- and right-hand tightening. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

maximum ring height h_1	10.7 mm
Width across flats 2	19 mm
maximum ring \varnothing D1	34.5 mm
Width across flats 1	17 mm
maximum ring height h_2	11.2 mm
overall length L	230 mm
maximum ring \varnothing D2	35.6 mm
Width across flats	metric
No. of teeth	5
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Type of product	Spanner

Accessories

Adapter for ratchet ring spanner Type 3	614850 3
---	----------