

**Garant****Circular saw blade, wood, alternating teeth universal, Blade Ø D: 350mm****Order data**

Order number	584075 350
GTIN	4045197220912
Item class	51S

**Description****Version:**

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

**Application:**

For circular, cross-cut, compound, and mitre saws.

**Universal** circular saw blade with long tool life and low noise, **unaffected by nails**. For **all wood types** and difficult materials in the building trade, including aluminium sections

**Note:**

**Further circular saw blades can be found in Group 17.**

Bore Ø: 30 mm

Drive holes number/Ø/pitch circle: 2/7/42 and 2/9/46 and 2/10/60 mm

Number of teeth: 54

Width of cut B: 3.2 mm

**Technical description**

Bore Ø	30 mm
Blade Ø D	350 mm

Number of teeth	54
Width of cut B	3.2 mm
Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade