

**Garant**
**Circular saw blade, wood, alternating teeth fine, Blade Ø D: 250mm**

**Order data**

Order number	584055 250
GTIN	4045197220820
Item class	51S

**Description**
**Version:**

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

**Application:**

For circular, cross-cut, compound, and mitre saws.

Type KW for **board materials with facing veneer and plastic covered on both sides as well as surface treated materials** with the highest cut quality requirements.

**Note:**

**Further circular saw blades can be found in Group 17.**

Bore Ø: 30 mm

Drive holes number/Ø/pitch circle: 2/7/42 and 2/9/46 and 2/10/60 mm

Number of teeth: 60

Width of cut B: 3.2 mm

**Technical description**

Number of teeth	60
Bore Ø	30 mm

Blade Ø D	250 mm
Width of cut B	3.2 mm
Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade