

Garant**DNMG 150408, Type: HB7120-1****Order data**

Order number	250868 HB7120-1
GTIN	4045197928726
Item class	21G

Description

DNMG 150408 HB7120-1 Grade: HB7120-1

Chip breaker: VG

Cutting depth a_p : 1.5 - 6 mmFeed f : 0.25 - 0.6 mm/rev.Cutting speed v_c main application: 70 - 240 m/min**Technical description**

Feed f	0.25 - 0.6 mm/rev.
Main application	M
Cutting depth a_p	1.5 - 6 mm
Grade	HB7120-1
Finishing/roughing assignment	Roughing
Cutting speed v_c main application	70 - 240 m/min
Tool material	Carbide

Cutting conditions	continuous
Corner radius	0.8 mm
Chip breaker	VG
ISO code indexable insert	DNMG 150408
Number of changes/inserts	4
Type of product	Indexable insert for turning