

Garant**DNMG 150404, Type: HB7120-1****Order data**

Order number	250670 HB7120-1
GTIN	4045197928627
Item class	21G

Description

DNMG 150404 HB7120-1 Grade: HB7120-1

Chip breaker: VS

Cutting depth a_p : 0.3 - 2 mmFeed f : 0.1 - 0.4 mm/rev.Cutting speed v_c main application: 90 - 290 m/min**Technical description**

Cutting depth a_p	0.3 - 2 mm
Main application	M
Cutting conditions	continuous
Tool material	Carbide
Corner radius	0.4 mm
Chip breaker	VS
Grade	HB7120-1

Cutting speed v_c main application	90 - 290 m/min
Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
ISO code indexable insert	DNMG 150404
Number of changes/inserts	4
Type of product	Indexable insert for turning