

Garant

Clamping toolholder SCSCR 45°, for indexable inserts CC., right-hand, Shank / insert size: 10/06mm



Order data

Order number	260000 10/06
GTIN	4045197929136
Item class	21T

Technical description

Overall length L	70 mm
suitable indexable insert	CC.. 0602..
Insert size	6 mm
Shank size	10 mm
ISO code toolholder	SCSCR/L 1010E06
Functional width L ₄	12 mm
Head length L ₁	12 mm
Pack of insert screws	269028 22
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8