

**Garant**

**Flap wheel roller, fleece (ZA) / fabric (ZA), Ø 100 × 100 mm, Grit equivalent:  
150FINE**

**Order data**

Order number	568471 150FINE
GTIN	4045197892355
Item class	51M

**Description****Version:**

Standard size Ø 100×100 mm or narrow version Ø 100×50 mm for grinding smaller areas.  
Mounting bore Ø 19 mm with multiple splines.

Combination of **abrasive fabric and fleece**.

Especially wear-resistant and fine-structured fleece with Zirconium Aluminium Oxide (ZA). **Ideal for use on stainless steel.**

**Application:**

For **light cleaning work** and a **uniform surface finish**.

**Note:**

For matching the width of narrow rollers Ø 100×50 mm use the spacer ring pack No. 568439.

**Technical description**

Grit equivalent	150
recommended speed	2800 min <sup>-1</sup>
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %

Roller Ø	100 mm
Roller width	100 mm
Product name attribute	Ø 100 × 100 mm
Type of product	Abrasive flap wheel roller, fleece

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		