

Garant

Clamping toolholder SCSCR 45°, for indexable inserts CC., right-hand, Shank / insert size: 16/09mm



Order data

Order number	260000 16/09
GTIN	4045197929150
Item class	21T

Technical description

ISO code toolholder	SCSCR/L 1616H09
Functional width L ₄	20 mm
Head length L ₁	20 mm
Insert size	9 mm
Pack of insert screws	269028 2
suitable indexable insert	CC.. 09T3..
Shim	269005 1
Overall length L	101 mm
Shank size	16 mm
Shim screw	269013 2
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15