

**Garant**

**Clamping toolholder SCSCCL 45°, for indexable inserts CC., left-hand, Shank / insert size: 20/09mm**



## Order data

Order number	260001 20/09
GTIN	4045197929266
Item class	21T

## Technical description

Head length L <sub>1</sub>	22 mm
Shank size	20 mm
Shim	269005 1
Insert size	9 mm
Functional width L <sub>4</sub>	25 mm
Shim screw	269013 2
suitable indexable insert	CC.. 09T3..
Pack of insert screws	269028 2
Overall length L	126 mm
ISO code toolholder	SCSCCL/L 2020K09
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15