

Garant
Clamping toolholder SCSCCL 45°, for indexable inserts CC., left-hand, Shank / insert size: 16/09mm

Order data

Order number	260001 16/09
GTIN	4045197929259
Item class	21T

Technical description

ISO code toolholder	SCSCR/L 1616H09
Shim	269005 1
Pack of insert screws	269028 2
Insert size	9 mm
Shank size	16 mm
Overall length L	101 mm
Shim screw	269013 2
Functional width L ₄	20 mm
suitable indexable insert	CC.. 09T3..
Head length L ₁	20 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15