



## Short drill chuck Form A, BT 40, Clamping range: 2,5-16mm



### Order data

Order number	303165 2,5-16
GTIN	4045197931856
Item class	32K

### Description

#### Version:

For clockwise and anticlockwise rotation.

- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

#### Supplied with:

**Clamping wrench.**

#### Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

Overhang dimension A	95 mm
Clamping range	2.5 - 16 mm
External Ø D	50 mm
Spare Torx® chuck key No. 625220	TX25
Adapter	BT 40
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	A
Balance quality G at rotational speed	G 6.3 at 12,000 rpm

Concentricity	≤ 50 μm
maximum tightening torque $M_{d\ max}$	≤ 14 Nm
Type of product	Short drill chuck