

Garant

Clamping toolholder SSSCL 45°, for indexable inserts SC., left-hand, Shank / insert size: 8/09mm



Order data

Order number	260707 8/09
GTIN	4045197937476
Item class	21T

Technical description

Insert size	9 mm
Overall length L	60 mm
suitable indexable insert	SC.. 09T3..
Pack of insert screws	269028 23
Functional width L ₄	13.25 mm
Head length L ₁	21 mm
Shank size	8 mm
ISO code toolholder	SSSCR/L 0808D09
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15