

Garant

Clamping toolholder SSSCR 45°, for indexable inserts SC., right-hand, Shank / insert size: 8/09mm



Order data

| | |
|--------------|---------------|
| Order number | 260706 8/09 |
| GTIN | 4045197937452 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| Shank size | 8 mm |
| suitable indexable insert | SC.. 09T3.. |
| Overall length L | 60 mm |
| Insert size | 9 mm |
| Pack of insert screws | 269028 23 |
| ISO code toolholder | SSSCR/L 0808D09 |
| Head length L ₁ | 21 mm |
| Functional width L ₄ | 13.25 mm |
| Standard | Works standard |
| Application type | right-hand |
| Through-coolant | no |
| Setting angle κ | 45 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15