

Garant
Short drill chuck Form AD, BT 40, Clamping range: 1-16mm

Order data

Order number	303171 1-16
GTIN	4045197937964
Item class	31B

Description
Version:

For clockwise and anticlockwise rotation.

Concentricity $\leq 20 \mu\text{m}$.

- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

With through coolant feed up to max. 50 bar.

Supplied with:

Clamping wrench.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping range	1 - 16 mm
Spare Torx® chuck key No. 625220	TX25
External \varnothing D	50 mm
Overhang dimension A	95 mm
Adapter	BT 40
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339

Shape	AD
Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 20 \mu\text{m}$
maximum tightening torque $M_{d\text{max}}$	$\leq 14 \text{ Nm}$
Type of product	Short drill chuck