

Garant**Indexable insert for turning CCGW 09T304, CBN (5° / 7°), Cutting edge version: G**

Order data

Order number	265415 G
GTIN	4045197895547
Item class	21H

Description

Version:

Fitted with 2 cutters.

Technical description

Feed f	0.04 - 0.12 mm/rev.
Cutting conditions	heavily interrupted
Cutting conditions	continuous
Cutting conditions	slightly interrupted
Cutting edge version	G
Cutting speed v_c main application	120 - 160 m/min
Tool material	CBN
Cutting depth a_p	0.03 - 0.12 mm

Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Grade	BU7220
ISO code indexable insert	CCGW 09T304
Number of changes/inserts	2
Product name attribute	BU7220
Type of product	Indexable insert for turning

User data

	Suitability	V _c	ISO code
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
continuous	suitable		
irregular	suitable		
interrupted	suitable		
dry	suitable		