


Garant**DNMG 150404, Type: HB7020****Order data**

Order number	250670 HB7020
GTIN	4045197948915
Item class	21G

Description

DNMG 150404 HB7020 Grade: HB7020
Chip breaker: SS
Cutting depth a_p : 0.3 - 2 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 150 - 400 m/min

Technical description

Cutting depth a_p	0.3 - 2 mm
Finishing/roughing assignment	Finishing
Grade	HB7020
Feed f	0.1 - 0.4 mm/rev.
Tool material	Carbide
Corner radius	0.4 mm
Cutting speed v_c main application	150 - 400 m/min

Cutting conditions	slightly interrupted
Chip breaker	SS
Main application	P
ISO code indexable insert	DNMG 150404
Number of changes/inserts	4
Type of product	Indexable insert for turning