


Garant**DNMG 150408, Grade: HB7035-1**

Order data

Order number	250672 HB7035-1
GTIN	4045197949028
Item class	21G

Description

DNMG 150408 HB7035-1 Grade: HB7035-1

Chip breaker: SS

Cutting depth a_p : 0.3 - 2 mmFeed f : 0.1 - 0.4 mm/rev.Cutting speed v_c main application: 120 - 350 m/min

Technical description

Cutting depth a_p	0.3 - 2 mm
Grade	HB7035-1
Main application	P
Finishing/roughing assignment	Finishing
Cutting conditions	heavily interrupted
Corner radius	0.8 mm
Feed f	0.1 - 0.4 mm/rev.

Tool material	Carbide
Chip breaker	SS
Cutting speed v_c main application	120 - 350 m/min
ISO code indexable insert	DNMG 150408
Number of changes/inserts	4
Type of product	Indexable insert for turning