

Garant**DNMG 150408, Type: HB7010-1****Order data**

Order number	250868 HB7010-1
GTIN	4045197949172
Item class	21G

Description

DNMG 150408 HB7010-1 Grade: HB7010-1
Chip breaker: SG
Cutting depth a_p : 1.5 - 6 mm
Feed f : 0.25 - 0.6 mm/rev.
Cutting speed v_c main application: 100 - 375 m/min

Technical description

Main application	P
Finishing/roughing assignment	Roughing
Cutting speed v_c main application	100 - 375 m/min
Cutting conditions	continuous
Feed f	0.25 - 0.6 mm/rev.
Grade	HB7010-1
Chip breaker	SG

Tool material	Carbide
Corner radius	0.8 mm
Cutting depth a_p	1.5 - 6 mm
ISO code indexable insert	DNMG 150408
Number of changes/inserts	4
Type of product	Indexable insert for turning