

**Garant****GARANT Master Tap machine tap HSS-E-PM, ALTiX, UNF: 10-32****Order data**

Order number	133410 10-32
GTIN	4045197899903
Item class	11I

**Description****Version:**

**GARANT Master Tap general-purpose tap**, designed for use on a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

**Application:**

**For UNF unified fine threads ASME – B1.1.**

Thread type: UNF

Tool material: HSS E PM

Standard: DIN 371

Threads per inch: 32

Thread Ø: 4.83 mm

Overall length L: 70 mm

Shank Ø D<sub>s</sub>: 6 mm

Shank square □: 4.9 mm

Tapping hole Ø: 4.1 mm

**Technical description**

Thread depth	14.49 mm
Overall length L	70 mm
Thread Ø	4.83 mm
Tool material	HSS E PM
Thread type	UNF

Standard	DIN 371
Tapping hole $\varnothing$	4.1 mm
Number of cutting edges Z	3
Threads per inch	32
Shank $\varnothing D_s$	6 mm
Thread size	10-32 UNF
Thread pitch	0.794 mm
Shank square $\square$	4.9 mm
Number of clamping slots	3
Series	Master Tap
Coating	AlTiX
Flank angle	60°
Tolerance class	2BX
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	30 m/min	P

Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	8 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	10 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		