

**Garant****Burr Z FINE – very fine, Carbide, Type: M1225****Order data**

Order number	540440 M1225
GTIN	4045197967206
Item class	51D

**Description****Version:**Shank  $\varnothing$  6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Pointed cone shape** (SKM).

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Head $\varnothing$	12 mm
Shank $\varnothing$	6 mm
Overall length	65 mm
Tooth type abbreviation	Z FINE
Shape description	pointed cone
Toothing grit designation	very fine
Shape	M1225
Head length	25 mm
Series	Tooth configuration Z FINE
Tool material	Carbide

Type of product

Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		