


HOLEX**Burr Z7 – medium, diamond cut, Carbide, Type: H1230****Order data**

Order number	540750 H1230
GTIN	4045197967220
Item class	52D

Description**Version:**

Shank Ø 6 mm.

HOLEX burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape description	flame
Head Ø	12 mm
Type of cut	staggered teeth
Toothing grit designation	medium
Shape	H1230
Overall length	75 mm
Shank Ø	6 mm
Tooth type abbreviation	Z7

Head length	30 mm
Series	#Tooth configuration Z7
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		