

Garant
Steel boring bar A.. SCLDR, for indexable inserts CDCT, right-hand, Shank \varnothing / insert size: 8/S4mm

Order data

Order number	268717 8/S4
GTIN	4045197923745
Item class	21V

Technical description

Overhang L_1	24 mm
Setting angle κ	95 degrees
Centre offset L_3	4.7 mm
suitable indexable insert	CDCT S4010.
ISO code toolholder	A08X SCLDR/LS4
Pack of insert screws	269028 10
Overall length L	76 mm
Insert size	4 mm
Minimum pre-drill $\varnothing D_{\min}$	9.05 mm
Clamping height L_2	7.49 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6