

**Garant**
**Four-way ratchet ring spanner "4 in 1", Type: 16-19**

**Order data**

Order number	614847 16-19
GTIN	4045197972903
Item class	61B

**Description**
**Version:**

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Width across flats 1: 16 mm

Width across flats 2: 17 mm

Width across flats 3: 18 mm

Width across flats 4: 19 mm

overall length L: 230 mm

maximum ring  $\varnothing$  D1: 31.5 mm

**Technical description**

Width across flats	metric
Width across flats 1	16 mm
Width across flats 4	19 mm
maximum ring height $h_2$	21.9 mm
maximum ring $\varnothing$ D2	33.5 mm
Width across flats 2	17 mm
overall length L	230 mm
maximum ring height $h_1$	20.2 mm

Width across flats 3	18 mm
maximum ring $\varnothing$ D1	31.5 mm
No. of teeth	72
Working arc	5°
Material	Chrome vanadium steel
Surface	matt chrome-plated
Ratchet reversible	yes
Type of product	Spanner