



Double ratchet ring spanner, Widths across flats: 30X32mm



Order data

Order number	614843 30X32
GTIN	4045197973375
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths. Reversible for left- and right-hand tightening, plus centre position. With unequal jaw widths, deep cranked. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

Width across flats	metric
Width across flats 1	30 mm
maximum ring \varnothing D1	60 mm
maximum ring height h_2	35 mm
maximum ring height h_1	34 mm
Width across flats 2	32 mm
overall length L	380 mm
maximum ring \varnothing D2	64.5 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Ring end cranked	yes
Ratchet reversible	no
Type of product	Spanner