

HOLEX**Flap wheel roller M14 Fleece wave form, Ø 100 × 50 mm, Grit equivalent: 180****Order data**

Order number	566375 180
GTIN	4045197973115
Item class	52M

Description**Version:**

Sinusoidal abrasive fleece with regular aluminium oxide (A) without cut edges.

Application:

For **matting** and **polishing** without abrupt changes in texture.

Technical description

recommended speed	2800 min ⁻¹
maximum speed	6000 min ⁻¹
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Thread	M14
Product name attribute	Ø 100 × 50 mm
optimised for material	INOX
optimised for material	Steel

maximum circumferential speed	30 m/s
Type of product	Flap wheel roller fabric, slit

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Carbide (HM)	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
dry	suitable		