

Garant

Mini grinding point fine, AR, Type: KU10



Order data

Order number	550400 KU10
GTIN	4045197975331
Item class	51E

Description

Version:

GARANT grinding points (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Ceramic bonded grinding points in **pink aluminium oxide (AR)**. Medium-hard version.

Fine grit. Shank \varnothing 3 mm, shank length 30 mm.

Application:

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

Grinding medium code: A

Head \varnothing : 10 mm

Head length: 10 mm

Shank \varnothing : 3 mm

Technical description

Shank \varnothing	3 mm
Grit designation	fine
Head \varnothing	10 mm
Head length	10 mm

Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Product name attribute	AR
Type of product	Grinding point