

Garant**DNMG 150412, Type: HB7120-1****Order data**

Order number	250869 HB7120-1
GTIN	4045197928740
Item class	21G

Description

DNMG 150412 HB7120-1 Grade: HB7120-1

Chip breaker: VG

Cutting depth a_p : 1.5 - 6 mmFeed f : 0.25 - 0.6 mm/rev.Cutting speed v_c main application: 70 - 240 m/min**Technical description**

Cutting depth a_p	1.5 - 6 mm
Main application	M
Chip breaker	VG
Tool material	Carbide
Cutting conditions	continuous
Finishing/roughing assignment	Roughing
Corner radius	1.2 mm

Cutting speed v_c main application	70 - 240 m/min
Grade	HB7120-1
Feed f	0.25 - 0.6 mm/rev.
ISO code indexable insert	DNMG 150412
Number of changes/inserts	4
Type of product	Indexable insert for turning