

Garant
Clamping toolholder SCSCR 45°, for indexable inserts CC., right-hand, Shank / insert size: 25/12mm

Order data

Order number	260000 25/12
GTIN	4045197929198
Item class	21T

Technical description

ISO code toolholder	SCSCR/L 2525M12
Shim	269005 6
suitable indexable insert	CC.. 1204..
Shank size	25 mm
Functional width L ₄	32 mm
Shim screw	269013 5
Pack of insert screws	269028 20
Head length L ₁	27 mm
Insert size	12 mm
Overall length L	151 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15