

**Short drill chuck Form A, SK 50, Clamping range: 2,5-16mm****Order data**

Order number	302575 2,5-16
GTIN	4045197931849
Item class	32K

Description**Version:**

For clockwise and anticlockwise rotation. Internal thread for manual clamping.

Application:

For clamping drills, countersinks, and reamers on milling machines.

Supplied with:

Supplied with Torx® chuck key with T-handle, for optimum clamping force.

Technical description

Overhang dimension A	85 mm
External Ø D	56 mm
Clamping range	2.5 - 16 mm
Spare chuck key	SW6
Adapter	SK 50
Arbor standard	DIN 2080
Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 50 µm
maximum tightening torque $M_{d\max}$	≤ 14 Nm

Type of product

Short drill chuck