

Garant

**Steel boring bar A.. SVLCR 95°, for indexable inserts VC., right-hand, Shank
Ø / insert size: 10/07mm**


Order data

Order number	261346 10/07
GTIN	4045197941459
Item class	21T

Technical description

Overall length L	100 mm
Minimum pre-drill Ø D _{min}	12.5 mm
Neck width L ₄	7.5 mm
Centre offset L ₃	7 mm
ISO code toolholder	A10H SVLCR/L07
suitable indexable insert	VC.. 0702..
Clamping height L ₂	9 mm
Head length L ₁	22 mm
Pack of insert screws	269028 27
Setting angle κ	95 degrees
Insert size	7 mm
Usable depth T	5 mm
Shank Ø D _s	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659905 200
Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659956 200
Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX6	675155 TX6