

Garant

Steel boring bar A.. SVJCR 142°, for indexable inserts VC., right-hand, Shank Ø / insert size: 10/07mm


Order data

Order number	261338 10/07
GTIN	4045197941268
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	13 mm
ISO code toolholder	A10K SVJCR/L07
Centre offset L_3	1.5 mm
Clamping height L_2	9 mm
Head length L_1	18 mm
Overall length L	125 mm
suitable indexable insert	VC.. 0702..
Neck width L_4	6.3 mm
Insert size	7 mm
Setting angle κ	142 degrees
Pack of insert screws	269028 27
Shank Ø D_s	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6