

**Garant**

**Steel boring bar A.. SVLCL 95°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 16/07mm**

**Order data**

Order number	261347 16/07
GTIN	4045197941510
Item class	21T

**Technical description**

Centre offset $L_3$	11 mm
Overall length L	150 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
suitable indexable insert	VC.. 0702..
ISO code toolholder	A16M SVLCR/L07
Setting angle $\kappa$	95 degrees
Clamping height $L_2$	15 mm
Insert size	7 mm
Pack of insert screws	269028 27
Head length $L_1$	36 mm

Neck width L <sub>4</sub>	14.5 mm
Usable depth T	5 mm
Shank Ø D <sub>s</sub>	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659905 200
Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659956 200
Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX6	675155 TX6