

Garant

**Steel boring bar A.. SVJCL 142°, for indexable inserts VC.., left-hand, Shank
Ø / insert size: 12/07mm**


Order data

Order number	261339 12/07
GTIN	4045197941282
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	13 mm
ISO code toolholder	A12L SVJCR/L07
Centre offset L_3	2 mm
suitable indexable insert	VC.. 0702..
Setting angle κ	142 degrees
Clamping height L_2	11 mm
Insert size	7 mm
Pack of insert screws	269028 27
Overall length L	140 mm
Neck width L_4	7.8 mm
Head length L_1	18 mm
Shank Ø D_s	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6