

**Garant**
**Arbor for screw-in milling cutters with thread, SK 40, Thread M×length L1:  
M16X231**

**Order data**

Order number	301313 M16X231
GTIN	4045197942852
Item class	31A

**Description**
**Version:**

**Vibration damped version, arbor with vibration-damping core.**

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

**Technical description**

L <sub>2</sub>	7.5 mm
Bore Ø D <sub>1</sub>	17 mm
External Ø D	48 mm
Overhang dimension A	250 mm
Thread M	M16×231
Ø D <sub>2</sub>	29 mm
Reach L <sub>1</sub>	231 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor