

Garant**Indexable insert for turning RC.X 1003, for medium machining, Grade: HU7310-1****Order data**

| | |
|--------------|-----------------|
| Order number | 260640 HU7310-1 |
| GTIN | 4062406058401 |
| Item class | 21G |

Technical description

| | |
|--------------------------------------|------------------------------------|
| Grade | HU7310-1 |
| Finishing/roughing assignment | Skrubbearbejdning-sletbearbejdning |
| Tool material | Carbide |
| Main application | N |
| Cutting conditions | continuous |
| Feed f | 0.1 - 0.3 mm/rev. |
| Chip breaker | AM |
| Cutting depth a_p | 0.5 - 2 mm |
| Cutting speed v_c main application | 350 - 600 m/min |
| Coating | uncoated |

| | |
|---------------------------|------------------------------|
| ISO code indexable insert | RCGX 1003 |
| Number of changes/inserts | 2 |
| Tolerance | G |
| Type of product | Indexable insert for turning |