


Garant**CNMG 120412, Grade: HB7210-1**

Order data

Order number	250160 HB7210-1
GTIN	4062406058906
Item class	21G

Description

CNMG 120412 HB7210-1 Grade: HB7210-1

Chip breaker: GM

Tolerance: M

Cutting depth a_p : 0.4 - 6.5 mm

Feed f : 0.3 - 0.7 mm/rev.

Cutting speed v_c main application: 100 - 450 m/min

Technical description

Cutting depth a_p	0.4 - 6.5 mm
Grade	HB7210-1
Tool material	Carbide
Main application	K
Corner radius	1.2 mm
Chip breaker	GM

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Cutting conditions	slightly interrupted
Feed f	0.3 - 0.7 mm/rev.
Cutting speed v_c main application	100 - 450 m/min
Coating	TiCN
ISO code indexable insert	CNMG 120412
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning