

Garant

Fixed solid carbide lathe centre 60°, very large Ø / Morse taper: 40/3



Order data

Order number	323200 40/3
GTIN	4045197947680
Item class	31Z

Description

Version:

- **High-precision solid carbide tip. Close-fitting carbide design for optimum stability and freedom from breakage, no additional safety equipment required.**
- **Tip angle 60°.**
- **High surface quality on the shank for optimum fit.**
- **Complete tool hardened and ground.**
- **With carbide tips for applications with high wear.**

Description:

Lathe centres are mainly used on lathes to support long and slim workpieces, since with these workpieces there would otherwise be a risk of the workpiece bending or moving around as a result of the forces generated.

The lathe centre is secured with a Morse taper. The workpiece is clamped in the chuck and a counterbore is added using a centre drill. After re-clamping, the lathe centre is then inserted.

Application:

For grinding high-precision components.

Optional extras:

Draw-off nut No. 323230.

Note:

Order the draw-off nut separately. Geometric dimensions to DIN 806 E.

Head length L: 44 mm

External Ø D: 40 mm

Ø d: 25 mm

maximum radial run-out: 0.001 mm

Technical description

Head length L	44 mm
External Ø D	40 mm
maximum radial run-out	0.001 mm
Ø d	25 mm
Morse taper	3
Type of product	Centring drill